

Show Presentation

We look forward seeing you at : Booth no. J37 Hall 98






Quattro pack machine: TWQ

- Versatile VFFS with small footprint and stable operation.
- Capable speed 100 bags/min.





Pillow bag

Quattro-pack 3-sided seal bag

Auger Filling Machine : FRJB

- Self-standing auger filler can be operated either by touch panel or foot switch.

- The demonstrated FRJB is equipped with degassing device that vacuums the air contained in the powder out of filler for preventing late-dropping of powder and reducing the powder dust.



with degassing

without degassing



Filling test in Tam laboratory

Tam recommends filling test for confirming the powder nature and the required specification would fit with the filling machine. Please contact us.



